



PRVS/PRTS

Perforated diffuser
Return
T-bar mounted in modular ceiling
Removable

Available types

P R - S - - -

- P** perforated ceiling diffuser
- R** return

- Face plate (passe-partout)

- V** flat
- T** t-bar mounted T24, 8 mm dropped (only in combination with T-profile)

- S** modular ceiling panel size 600 mm, removable

- Ceiling version (see table on page 26)

- I** T-bar mounted
- A** concealed panel (concealed ceiling version)
- B** concealed panel (concealed ceiling version)
- C** concealed panel (concealed ceiling version)

- Accessories

- O** none
- F** fitted with a filter

- Version

- A** round top connection
- N** without plenum, with separate sightproof cover
- U** assembled, uninsulated plenum box
- R** assembled, internally insulated plenum box
- Z** square top connection

SA-Select

Check SA-Select to create extended order codes and selection details online. **NB!** At this moment, SA-Select is only available in Dutch. But it is possible to create extended order codes and selection details online.

Use

The PRVS perforated diffuser is suitable for air extraction and has the same appearance as the supply diffuser PTVS. The diffuser has a removal face plate on the sight side, it can be T-bar mounted in a modular ceiling with a panel size of 600 mm and can be fitted with an insulated or uninsulated plenum box, which is supplied ready assembled. The perforated diffuser, type PRTS, is equipped with an 8 mm lowered face plate. As standard, the plenum box is equipped with 8 mm hanging holes in the raised edge of the plenum.

Version

Perforated diffuser
 Front face: steel
 Post-treatment: epoxy
 Colour: white RAL 9010, optional RAL colour of your choice


Plenum box

Material: sendzimir galvanised steel
 Internal insulation: 1/2" duct liner
 Post-treatment: none

Optional

Panel size: up to 750 mm
 Plenum box: flat-sided
 Face plate: other than inlay T24, lowered by 8 mm on request

Dimensions



Available dimensions and sizes

model	A	D1	D2	T	P
250	242	123	123	70	235
300	307	158	158	70	270
400	382	198	198	75	315
500	477	248	198	85	325
550	551	313	248	105	395

Weight

model	type	
	without plenum OA	with plenum OR/OU
	kg	kg
250	2.4	3.2
300	2.4	4.1
400	2.3	4.9
500	2.2	5.7
550	2.5	7.2

Note

- The listed dimensions are in mm.
- Dimensions t-bar mounted dropped:
 - T-bar mounted 24 mm (standard): X = 595, Y = 8, Z = 574
 - T-bar mounted 15 mm: X = 595, Y = 8, Z = 583
- Information regarding flat-sided plenum boxes is available on our [website](#).

Selection details

PRVS-OA, PRVS-OR and PRVS-OU

air volume		round connection		
m ³ /s	m ³ /h	model	Δp_s Pa	L_{PA} dB(A)
0.015	54	250	1	-
0.020	72	250	3	-
0.025	90	250	4	-
		300	1	-
0.030	108	250	6	-
		300	2	-
0.040	144	250	11	-
		300	4	-
		400	1	-
0.050	180	250	16	12
		300	6	-
		400	2	-
0.060	216	250	24	17
		300	9	-
		400	3	-
0.080	288	500	3	-
		300	15	13
		400	6	-
		500	5	-
0.100	360	550	3	-
		300	24	19
		400	9	-
		500	8	-
0.125	450	550	4	-
		400	14	15
		500	12	15
0.150	540	550	6	-
		400	21	20
		500	18	20
		550	9	10
0.200	720	500	31	27
		550	16	17
0.250	900	550	25	23
0.300	1080	550	35	28

PRVS-OZ and PRVS-ON

air volume		square connection		
m ³ /s	m ³ /h	model	Δp_s Pa	L_{PA} dB(A)
0.080	288	250	9	10
		300	3	-
0.100	360	250	13	15
		300	5	-
		400	2	-
0.125	450	250	21	21
		300	8	11
		400	3	-
0.150	540	250	30	25
		300	11	15
		400	4	-
		500	2	-
0.200	720	250	54	32
		300	20	22
		400	8	13
		500	3	-
0.300	1080	550	2	-
		300	45	32
		400	18	23
		500	7	14
0.400	1440	550	3	-
		300	79	39
		400	32	30
		500	13	21
0.500	1800	550	6	14
		400	49	35
		500	20	26
		550	10	19
0.600	2160	400	71	39
		500	29	31
		550	14	23
0.800	2880	500	51	37
		550	24	30
1.000	3600	550	38	36

Attenuation values plenum box (without end reflection)

model	attenuation values						
	125	250	500	1k	2k	4k	Hz
250	5	0	3	10	5	11	dB
300	3	1	6	7	7	9	dB
400	2	2	9	7	7	9	dB
500	2	4	9	7	7	10	dB
550	0	6	7	7	6	9	dB

General

- The assumed room attenuation is 10 dB.
- It is permitted to interpolate the interim values.

Concealed ceiling version

manufacturer	product/type	version
Ecophon	FocusTM Ds	B
	Hygiène LabotecTM Ds C1	B
	SombraTM Ds	B
	Combison UnoTM Ds	B
OWA	Cosmos	A
	Sinfonia	A
Rockfon	Sonar system D	A
	Krios System D	A
	Sonar system X	C
	Krios system X	C

